

WI-M-10-XX-@

(Extra Heavy-Duty 10 AWG, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-10-@ is 10 AWG, 1050/0.08 stranded, tinned copper wire with highly flexible 0.197" (5mm) diameter silicone jacket.
- Ratings:

Current	45 Amps @ 150°C
Voltage	600V
Dielectric Strength	2 KV/Min
Spark Test	6 KV
Bend Radius	3D
Rated Temperature	-40°C to 200°C
Temperature Rating	FT2
UL Safety Standard	UL 758
- Length: The "XX" in the model number indicated length in feet.
Standard lengths: 10', 25', 30', 50', and 100'
- Color: The "@" in the model number represents color.
Available colors: -0 Black, -2 Red

Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524