




Part Number : [150140629](#)

Product Description : 0.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 152.00mm Cable Length, Gold (Au) Plating, 29 Circuits

Series Number : 15014

Status : Active

Product Category : Flat-Flexible Cable (FFC)



Documents and Resources

Drawings

[150140629_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[1501400001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15014
Description	0.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 152.00mm Cable Length, Gold (Au) Plating, 29 Circuits
Product Name	Premo-Flex FFC Jumper
UPC	191130093571

Electrical

Current - Maximum per Contact	0.2A
Voltage - Maximum	N/A

Physical

Cable Length	152.00mm
Circuits (Loaded)	29
Contact Layout Type	A (same side)
Design Feature	Miniaturization
Material - Plating Mating	Gold
Net Weight	0.246/g
Packaging Type	Bag
Pitch - Mating Interface	0.25mm
Temperature Range - Operating	-40° to +105°C
Termination Style	FFC Connector

Wire/Cable Type	Flat Flexible Cable (FFC)
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Easy-On Front Flip FPC Connector, 0.25mm Pitch, Surface Mount, 1.20mm Height, Top Contact, Right-Angle, Low Halogen, 29 Circuits, 3000 Pieces per Reel	<u>5033002910</u>

This document was generated on May 24, 2026