





PRODUCT NUMBER	PITCH
HXxx00x000J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



Material:

- Item@ Insulating body: Thermoplastic (UL94V-0)
- Item@ Insulating cover: Thermoplastic (UL94V-0)
- Item@ Insulating lever: Thermoplastic (UL94V-0)
- Item@ Solder pin: Brass, Tin plated
- Item@ Spring clamp: Stainless steel

Electrical cULus

- Voltage rating: 300V
- Current rating: 8A
- Wire range:
- Solid wire(AWG): 16-26
- Stranded wire(AWG): 16-26
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:

N=Number of poles
Dim L=(N-1)×5.0+6.0
Dim B=(N-1)×5.0

Poles	Tolerance
1-4p	±0.15
5-9p	±0.20
10-14p	±0.30
15-19p	±0.40
20-24p	±0.50

PART NO.: HX xx 00 x 0 00J0 G

End stackable	No. of poles	Color	RoHS compliant
0	2	Black (RAL9005)	(lead<4%)
01	1 poles	Red (RAL3001/D)	In copper Alloy
02	2 poles	Orange(RAL2011/P)	
...	...	4 Yellow(RAL1018/A)	
...	...	5 Green(RAL6018/T)	
24	24 poles	6 Blue (RAL5015/A)	
		8 Grey(RAL7004/P)	
		9 White(RAL1102)	
		C Multiple colors	

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK											
litr ecn no dr date				tolerances unless otherwise specified								title									
				angles linear		X.±0.5		TERMINAL BLOCK													
						X.X±0.3		SPRING CLAMP, 90D WIRE INLET													
				X*±1°		X.XX±0.1		scale													
				dr		EVIN ZHONG		052614				dwg no				sheet 1 of 1				size	
				enr		EVIN ZHONG		052614				HXxx00x000J0G								A	
				chr		HANKE FENG		052614													
				appd		SHI JUN		052614													
sheet index		revision sheet		A 1																	