

Home: > [Datasheet](#)

Part Number: 76142-0021

Image not available

Status: Contact Molex
Series: [76142](#)
Category: Molex Parts

Go to [Part Detail](#)

 [CHECK DISTRIBUTOR INVENTORY](#)

 [Add to My Parts](#)

Series image - Reference only

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

[EU RoHS](#): ELV and RoHS Compliant

[China RoHS](#):

[REACH SVHC](#): Contains SVHC: No

[Low-Halogen Status](#): Low-Halogen



Product Compliance Statement

Part Detail

[COLLAPSE ALL](#)

General

Status	Contact Molex
Category	Molex Parts
Series	76142
UPC	887191308852

Physical

Flammability	94V-0
Net Weight	8.297/g

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

UL	E29179
----	--------

Material Info

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Molex Connectors

Wire-to-Board
Board-to-Board
Wire-to-Wire
Input/Output (IO)
FFC/FPC
Sockets

Other Products

Fiber Optic Products
Antennas
Industrial Automation
Membrane Switches
Copper Flex
PCB Assemblies
Woodhead Electrical
Solid State Lighting

Resources

Contact Us
Catalog
Cross-Reference
Industries
Literature
Product Name

Company Info

About Us
Careers
ecocare
Investors
Press Room
Shows & Events
Supplier Portal

Other Info

Feedback
Help
Legal Disclaimer
View Mobile Site
Privacy Policy
Sitemap

Stay Connected with Molex:

