



Load vacuum cover



(All contacts and grounds)







PCB layout, component side



Z (5:1)



Max. Temperature: 260°C during 10 seconds.
Find further technical information on DS 09550200302.

Part number	PL	Screw lock	Index designation
0955 415 6622 333	2	4-40 UNC	Samples
0955 415 3622 741	1	4-40 UNC	Reel packaging (140 connectors)
0955 415 6622 741	2	4-40 UNC	Reel packaging (140 connectors)
0955 415 7622 741	3	4-40 UNC	Reel packaging (140 connectors)
0955 415 3621 741	1	M3	Reel packaging (140 connectors)
0955 415 6621 741	2	M3	Reel packaging (140 connectors)
0955 415 7621 741	3	M3	Reel packaging (140 connectors)

Black insulator

All Dimensions in mm
Original Size DIN A3

Scale 2:1

Free size tol.

Ref.

Sub.

All rights reserved

Department EL PD

HARTING Electronics GmbH
D-32339 Espelkamp

Created by	Inspected by	Standardisation	Date	State
ZHUANGJ	LUOK	HOFFMANN	2018-11-29	Final Release

Title: D-Sub straight SMT 37-pole fem ass with screw lock and pad

Doc-Key / ECM-Nr.: 100236616/UGD/001/C 500000139800

Type: TB

Number: 0955415X62X

Rev.: C

Page: 1/1

Downloaded from Arrow.com.

A3