

Datasheet for part number TR1208RFS1NB

Our Catalog Part Number: TR1208RFS1NB
Our Global Manufacturing Part Number: 192922-1200
Brand: Cannon Product Category: Trident Product Line: Trident Series: TR

Product Datasheet	
Series	Trident Ringlock
Connector Type	Receptacle for Flange Mounting
Environmental Sealing	unsealed
Sealing Methode	no sealing
Shell Size	12
Contact Quantity	8
Contact Gender	Socket
Contacts included	No, order separately
Operating Voltage	48 Vac, 60 Vdc
Current Rating	Up to 13 A
Operating Temperature	-55°C to +105°C
Insulator Resistance	5000 Megaohms at 500 V dc
Durability	Up to 500 Mating Cycles
Flammability	UL94-V0
Salt Spray	48 hours
Vibration	10 g's peak, 10 to 500 Hz, 9 hours
Physical Shock	50 g's peak, 11msec., half-sine pulse
Insulator Material	Black Nylon
Coupling Nut Material	Nickel Plated Zinc Alloy
Sealing Grommet Material	Silicone Rubber
Mounting Style	Standard

Specifications and dimensions subject to change.