



+ CONNECTORS

AUTOMOTIVE SEALS & CAVITY PLUGS



✓ Active

TE CONNECTIVITY (TE)

SINGLE WIRE SEAL,HPF 1.2,RUBBER

TE Internal Number: 2297817-1

EU RoHS Compliant

EU ELV Compliant

Seal Type Wire Seal

Cavity Diameter 3.58 mm [.141 in]

Cable Insulation Diameter 1.4 – 1.6 mm [.055 – .063 in]

Material Silicone

Shore A Hardness 50

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

Single Wire Seal, HPF 1.2 Einzelleiterdichtung HPF 1.2

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Seal Type Wire Seal

Body Features

Material Silicone

Color Green

Dimensions

Cavity Diameter 3.58 mm [.141 in]

Cable Insulation Diameter 1.4 – 1.6 mm [.055 – .063 in]

Usage Conditions

Operating Temperature Range -40 – 150 °C [-40 – 302 °F]

Operating Temperature (Max) (°C) 105, 110, 120, 125, 130, 150

Operating Temperature (Max) (°F) 221, 230, 248, 257, 266, 302

Industry Standards

UL Flammability Rating None

Packaging Features

Packaging Method Bulk

Other

Shore A Hardness 50

Lubricant Content Yes

Statement of Compliance

Statement of Compliance

PDF