





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

914CE2-12




NOTES

1 - ZINC HOUSING FINISHED WITH GRAY PAINT

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 2.7 LB MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.01) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT	
RELEASE FORCE — — — 1.0 LB MIN	5A — 250 VAC 1/10HP — 125 OR 250 VAC  		
DIFFERENTIAL TRAVEL — — — .004 MAX			
OVERTRAVEL — — — — — .118 MIN			

914CE2-12

M

DRAWING
NUMBER

3

ISSUE

REPLACES

RELEASE NO. PR-7645

CHECK

REVISIONS

A CO-69061
S A V
31 AUG 91

CHECK

DDM/CAD

DRAWN

CHECK

91

3

SEPT

91