Part Number : 513820700
Product Description : MicroClasp Receptacle Housing, 2.00mm Pitch, Positive Lock, Single Row, 7 Circuits, White
Series Number : 51382
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

513820700_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

513820700.dxf

Specifications

561340000-AS-000.pdf

513829200-200.pdf

SPK-51382-001-001.pdf

513820000-PS-001.pdf

PS-51382-004-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	51382
Description	MicroClasp Receptacle Housing, 2.00mm Pitch, Positive Lock, Single Row, 7 Circuits, White
Application	Wire-to-Board
Component Type	Housing
Product Name	MicroClasp
UPC	800756632292

Agency

UL	E29179

Physical

Circuits (maximum)	7
Color - Resin	White
Flammability	94V-0

Downloaded from Arrow.com.

Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	372.100/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MicroClasp Vertical Single Row Headers	55932
MicroClasp Right-Angle Single Row Headers	55935

Use with Part(s)

Description	Part Number
Pre-Crimped Lead MicroClasp Female-to-MicroClasp Female, Tin (Sn) Plating, 150.00mm Length, 24 AWG, Black	797581001
Pre-Crimped Lead MicroClasp Female-to-MicroClasp Female, Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black	797581002
MicroClasp 2.00mm Pitch and MUO 2.5 Crimp Terminal, Female, Tin (Sn) Plated, 28-22 AWG, Copper Alloy, Reel	561349000
MicroClasp 2.00mm Pitch and MUO 2.5 Crimp Terminal, Female, Tin (Sn) Plated, 28-22 AWG,	561349100

Downloaded from Arrow.com.

Copper Alloy, Bag	
MicroClasp Terminal Position Assurance (TPA) Retainers	500638

Downloaded from Arrow.com.