




Technical drawing of a mechanical part, showing a cross-section with dimensions 5,3 and 8,2.

Performance level	PL2
Filter type	C
Capacitance	3900pF±20%
Working Voltage	100V
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB

			Dot.	Name	D-Sub, female, straight 9 Poles, with turned solder bucket, fixing hole All Dim. in mm Orig. Size DIN A 4	No?/stab/ Scale
			Detail.	8-JUL-02 CV		
			Insp.	12/01/12 JB		
			Stand.			
36283	12/01/12	SD				TB 09641117240 Sub.
32802	11/07/05	JMDR				
31058	8-JUL-02	CV				
Mod.	Dot.	Name				
HARTING EURL F-95972 Paris						Blatt/ Page 1 / 1