

Home	Products	Search	Support	About Us
------	----------	--------	---------	----------

[Home](#) > [Search Engine](#) > Catalog: AS-M15KAH-R

Sensors > Magnetic Switch

How to check EU RoHS Compliance of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specifications

Global Part Number	AS-M15KAH-R
Previous Part Number	
Supply Voltage	1.6 to 6.0V
Current Consumption	1.6 to 3.0?A
Operating Magnetic Field (H->L)	1.6mT max.
Operating Magnetic Field (L->H)	0.5mT min.
High Level Output Voltage	
Low Level Output Voltage	
Operating Temp. Range	-40 to +85℃
Storage Temp. Range	-50 to +125℃

Details

-  [Part Numbering](#)
-  [Appearance](#)
-  [Dimensions](#)
-  [Features](#)
-  [Caution](#)
-  [Notice_\(Storage_and_Operating_Conditions\)](#)
-  [Notice_\(Rating\)](#)
-  [Notice_\(Soldering_and_Mounting\)](#)

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	5000
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	
Box	

Please approve our product specifications or to transact the approval sheet for product specifications before ordering.
Please read rating and !Cautions first.
Product specifications in this catalog are as of November 2012
Please make sure to read the Murata's [Product Policy](#) ,too.

All products and company names herein are trademarks or registered trademarks of their respective owners.