Datasheet for part number DAM-15P

Our Catalog Part Number: DAM-15P
Our Global Manufacturing Part Number: 053512-0028
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M

Product Datasheet	
General	D*M High reliable D-Sub Connectors
Wire Gauge Range AWG	AWG 20-28
Mating Cycles	200
Contact Arrangement	15 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	7.5 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	Steel
Shell Finish	Yellow chromate over zinc
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Pin
Contact Type	Solder Pot
Contact Material	copper alloy
Contact Finish	Gold flash (4-10 microinch) over 100 microinch nickel
Hardware	.120" (3,05mm) Through Hole

Specifications and dimensions subject to change.

Downloaded from Arrow.com.