

214A332-3-0

TE Internal Number: 814299-000

Active

Molded Parts

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

Molded Part Type = D Subminiature Boot

Family Name = 214A3

Straight

General Purpose Application

10 Material Systems Code

View all Features

Quick Links

Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

Share

Print

Email

Documentation & Additional Information	
Product Drawings: Boot, Rectangular, Subminiature, Straight Overexpanded (PDF, English) Catalog Pages/Data Sheets: None Available Product Specifications: None Available Application Specifications: None Available Instruction Sheets: None Available CAD Files: None Available	Additional Information: Product Line Information Related Products: Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: Molded Part Type = D Subminiature Boot Family Name = 214A3 Angle = Straight Adhesive Description = Adhesive Purchased Separately. Size = 32 Mechanical Attachment: Adhesive Pre-Coating = Without Dimensions: Cable Diameter Range (mm [in]) = 8.10 - 14.00 [0.319 - 0.551] Connector Length (mm [in]) = 42.00 - 42.20 [1.654 - 1.661] Connector Width (mm [in]) = 10.70 [0.421] Body Features: Material = Semi rigid Modified Polyolefin Housing Features: Material Systems Code = 10	Configuration Features: Material Code = 3 Industry Standards: Government/Industry Qualification = No Approved Standards = DEF Std 59-97 Issue 3 Type DA, MIL-I-81765/1 Class I, UL224 E85831 RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Not relevant for lead free process RoHS/ELV Compliance History = Always was RoHS compliant Environmental: Operating Temperature (°C) = -55 - +135 Operation/Application: Application = General Purpose Purchasing Information: Adhesive Code = S1125 Other: Brand = Raychem Comment = Contact Raychem for additional adhesive and/or cut off boot length information