






PRODUCT NUMBER	PITCH
TJxx51x200J0G	5.08 mm



Material

- Item ① Clamp: Brass(CuZn) Ni plated
 - Item ② Terminal screw: Steel Zinc plating "-" slot type
 - Item ③ Female contact: High conductivity copper, Tin plated
 - Item ④ Terminal Cover: Thermoplastic (UL94V-0)
 - Item ⑤ Terminal housing: Thermoplastic (UL94V-0)
 - Item ⑥ With flange screw: Steel Zinc plating M2.5"/+/-" slot type
- Electrical cULus/VDE/TUV
- Voltage rating: 300VAC/300VAC/300VAC
 - Current rating: 20A/20A/20A
 - Wire range: 2.5mm²/0.34-2.5mm
 - Solid wire(AWG): 12-24/14-22
 - Stranded wire(AWG): 12-24/14-22
 - Torque: 5Lb-In/0.5Nm/0.56Nm
 - Screw: M3
 - Wire strip length: 7-8mm
 - Withstanding Voltage: 1.6KV/2.5KV/2.5KV
 - Operating temperature: -40°C to +115°C
 - Safety Approval: cULus VDE TÜV

PART NO.: TJ xx 51x 2 00J0 G

Dimension

Dimension	
Dim L	Nx5.08
Dim B	(N-1)x5.08
Dim C	(N+2)x5.08
Dim D	(N+1)x5.08

N= Number of poles

Poles	Tolerance
2P-7P	±0.15
8P-12P	±0.25
13P-18P	±0.30
19P-24P	±0.40

No. of poles	Color	RoHS compliant
02 2 poles	0 Black (RAL9005)	(lead<4%)
03 3 poles	2 Red (RAL3001/D)	In copper Alloy
...	3 Orange(RAL2011/P)	
...	4 Yellow(RAL1018/A)	
24 24 poles	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family	
ltr ecn no dr date				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK	
				tolerances unless otherwise specified		MM	title	
				angles	X.±0.5		TERMINAL BLOCK	
				flat	X.X±0.3		PLUGGALBE PLUG,DOWN CONTACT,WITH FLANGE	
				X'±1"	X.XX±0.1	scale	dwg no sheet 1 of 1 size	
				dr	HANKE FENG 032214		TJxx51x200J0G A4	
				enrg	HANKE FENG 032214		type	
				chr	SHI JUN 032214		CUSTOMER Drawing	
				appd	SHI JUN 032214			
sheet index	revision	A	1					