

## SEK CAB FLAT STD AWG28/7 60P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 060 7001
Specification	SEK CAB FLAT STD AWG28/7 60P 30,48m
HARTING eCatalogue	<a href="https://harting.com/09180607001">https://harting.com/09180607001</a>

### Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)

### Version

Cable length	30.48 m
Number of cores	60
Core structure	AWG 28/7

### Technical characteristics

Limiting temperature	-30 ... +105 °C unmoved -20 ... +105 °C moved
Impedance	100 Ω
Insulation resistance @ 20 °C	≥20 MΩ x km

### Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Net weight	3,720 g
Net weight	106 g/m
Country of origin	Germany
European customs tariff number	85444993
GTIN	5713140025349
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249
UNSPSC 24.0	26121609