

## EM 8/30

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### System accessory

Discover a wide range of accessories for your u-remote system - the ideal addition to make your applications even more efficient and flexible.

### General ordering data

Version	EM, Terminal marker, 32.4 x 7.2 mm, Pitch in mm (P): 7.20 Weidmueller, Transparent
Order No.	<a href="#">1806120000</a>
Type	EM 8/30
GTIN (EAN)	4032248275298
Qty.	50 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	3 mm	Depth (inches)	0.1181 inch
Height	32.4 mm	Height (inches)	1.2756 inch
Width	7.2 mm	Width (inches)	0.2835 inch
Net weight	0.6 g		

**Temperatures**

Operating temperature range	-40...80 °C
-----------------------------	-------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General data**

Orientation of print	horizontal	
Width	7.2 mm	
UL 94 flammability rating	HB	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Colour	Transparent	
Halogen	No	
Basic material	Polypropylene	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Component part
Number of markers per combination	1 Component part = Terminal marker	
Operating temperature range	-40...80 °C	
Application/manufacturer	Weidmueller	

**Connector markers**

Pitch in mm (P)	7.20 mm
-----------------	---------

**Classifications**

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		