




PANDUIT PART NO.	RECOMMENDED FASTENER	'A'	'B'	'C'	'D'	'E'	'F'	'G'	'H'	'I'	WEIGHT		PRODUCT COMPATIBLE WITH CABLE TIE CROSS-SECTION(S)
											lbs/100	pcs	
SGTM2S8- TMSG2S8-	#8 (M4) SCREW	0.66 [16.7]	0.48 [12.2]	0.34 [8.6]	0.25 [6.3]	0.09 [2.3]	0.22 [5.6]	0.15 [3.8]	0.333 [8.7]	0.18 [4.6]	0.180 [81.6]		S, I, M SG100M, SG150I, SG200S, SG250S, SG300S, SG370S



SECTION A - A



NOTES:
1. SEE CURRENT PRICE SHEET FOR PART
NUMBER SUFFIX DESIGNATION FOR
PACKAGE SIZE.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G02789BE_PB_SGTM2S8_02

PANDUIT

CORP. TINLEY PARK, ILLINOIS

TIE MOUNT - (SUPER GRIP TIES)
SGTM2S8- & TMSG2S8-

											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ± 5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	3/9/06	JAD		UPDATE CABLE TIE CALLOUTS IN TABLE	GB2987BE	2					DRAWN BY TMSA	MAT'L: NYLON 6/6	SCALE NONE	
1	8-24-05	TMSA		ADDED PART NUMBER SGTM2S8-	GB2987BE	1					DATE 03-22-05		DRAWING NO.	
R	03-22-05	TMSA		INITIAL RELEASE	GB2987BE	R					CHK'D		GB2987BE	
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP					A SIZE	