

molex

Part Number : [1301020125](#)

Product Description : Super-Safeway Rubber Hand Lamp with 100W, Screw Release Vinyl Coated Guard with Reflector, with Switch and Side Outlet, Cord Length 15.24m (50.0'), Cord Type 16/3 SOOW

Series Number : 130102

Status : Obsolete

Product Category : Lamps and Lights

Engineering Part Number : 106USIB163



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Lamps and Lights
Series	130102
Description	Super-Safeway Rubber Hand Lamp with 100W, Screw Release Vinyl Coated Guard with Reflector, with Switch and Side Outlet, Cord Length 15.24m (50.0'), Cord Type 16/3 SOOW
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678899225

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	Yes
Guard Type	Insulated, Reflector, Screw Release
Height	374.65mm (14.750")
Lamp Type	A21

Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	3029.994/g
Outlet	Side
Packaging Type	Carton

This document was generated on May 27, 2026

Obsolete