



Part Number : [2043141130](#)
Product Description : Sentrality 3.40mm Right-Angle Screw Mount Pin, 26.00mm Engagement Length, Tray
Series Number : 204314
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[2043141130 sd.pdf](#)
[2043141120-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2204090000-AS-000.pdf](#)
[2204090000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	204314
Description	Sentrality 3.40mm Right-Angle Screw Mount Pin, 26.00mm Engagement Length, Tray
Application	Board-to-Board, Busbar-to-Board, Power
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Header
Product Name	Sentrality
UPC	196823766015

Electrical

Current - Maximum per Contact	120.0A
Voltage - Maximum	1000V

Physical

Breakaway	No
Circuits (Loaded)	1

Circuits (maximum)	1
Diameter	3.40mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Height Above Board	17.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Net Weight	9.883/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Retention	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Screw Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality 3.40mm Right-Angle Socket Assemblies	<u>205000</u>
Sentrality Top-entry Knurled Press-Fit Socket Assemblies with Self-alignment Capability	<u>204313</u>
Sentrality Top-entry Knurled Press-Fit Socket Assemblies	<u>204316</u>
Sentrality Top-entry Surface Mount Socket Assemblies	<u>204318</u>
Sentrality Top-entry Surface Mount Socket Assemblies with	<u>204365</u>

Self-alignment Capability	
Sentrality Surface Mount Socket Assemblies	<u>212195</u>
Sentrality 3.4mm Eye-of-Needle Press-Fit Socket Assemblies	<u>214132</u>

This document was generated on May 05, 2026