© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved







✔ Active

TE CONNECTIVITY (TE)

NI-CHROME WIRE 250 TAB 20-15 NICKEL CRS

FASTON | 250

1217918-1
TE Internal Number: 1217918-1

EU RoHS Compliant
EU ELV Compliant

Terminal Type Tab

Wire Size (AWG) 20 – 15

Wire Size (mm^2) .5 – 1.5

Mating Tab Width 6.35 mm [.25 in]

Mating Tab Thickness .81 mm [.032 in]

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION —

Product Drawings

TAB, .250 SERIES FOR NI-CHROME WIRE

PDF **(TIFF AVAILABLE)**

English

CAD Files

3D PDF

PDF

3D

Customer View Model

Downloaded from Arrow.com.

2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminates To Wire & Cable
FASTON No
Insulated Wire Support No
Contact Base Material Steel
Disconnect Type Quick Connect
Insertion Force Normal
Insulated No
Wire/Cable Type Discrete Wire
Wire Stop No
Wire/Cable Composition Stranded

Configuration Features

Connection Capacity Single

Body Features

Fully Insulated No
Plating Material Nickel
Plating Thickness (µin) 1000

Contact Features

Terminal Type Tab
Terminal Orientation Straight
Barrel Type Open
Crimp Type F-Crimp

Mechanical Attachment

Mating Retention Type Hole

Dimensions

Downloaded from Arrow.com.

Wire Size (AWG) 20 – 15
Wire Size (mm²) .5 – 1.5
Mating Tab Width 6.35 mm [.25 in]
Mating Tab Thickness .81 mm [.032 in]
Receptacle Stock Thickness .81 mm [.032 in]
Overall Length 39.62 mm [1.56 in]

Industry Standards

UL Rating Listed

Packaging Features

Packaging Method Reel
Packaging Quantity 3000

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.