

96MPI7-3.4-8M11T



- Intel 2nd Generation Core i7-2600
- Up to 3.8 GHz
- 8 MB Cache
- LGA1155

Datasheet (PDF)

Get Quote

Product Specifications

 Download S

Part Number	96MPI7-3.4-8M11T		
Details			
CPU			
Market	Desktop		
Manufacturer	INTEL		
Processor Number	Core i7-2600		
Code Name	Sandy Bridge		
Socket Type	LGA1155		
Processor Base Frequency	2.8 GHz		
Bus Speed	5 GT/s		
Cache Memory	8 MB		
Smart Cache	8 MB		
Graphic Processor	Intel HD Graphics P2000		
Manufacturing Technology	32 nm		
sSpec	SR00B		
Thermal Design Power (TDP)	95 W		
# of Cores	4		
64 bit Support	YES		
Embedded	Yes		
Package	Tray		
Warranty	1 year		



Need more info? Talk to our Online Rep!

[Live Chat](#)

[Inquiry Form](#)

Related Materials

All

News (7)

Catalog (1)

【Phase Out】Intel CPU
Celeron, Pentium, Core and Xeon

8/03/2018 | News

【Phase In】Intel Xeon E
proessor

7/30/2018 | News

【Phase In】Intel Coffee Lake
CPU

6/05/2018 | News

2018 Advantech Ce
Peripherals Catalog

5/31/2018 | Catalog

How Can We Help?



Support



Live Chat



1-888-576-9668

ADVANTECH

- [Company Information](#)
- [Investor Relations](#)
- [Contact Us](#)
- [Corporate Citizenship \(CSR\)](#)
- [Global Exhibitions](#)
- [Careers](#)