



REV.	DATE	DESCRIPTION
A	07/21/05	UPDATE DRAWING FORMAT



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
 2. CRIMPED CONTACT PIN
SQ. CRIMP SIZE 0.7mm
 3. MAX. PANEL THICKNESS = 2.4mm

						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex									
8									DRAWN	G.R.S.	07/21/05										
7	HEAT SHRINK TUBE				BLACK	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”		CHECKED				PART DESCRIPTION								
6	FERRULE		COPPER	GOLD	1	ISSUED					SMB MINI BULKHEAD JACK – 75ohm (FOR RG–179/U CABLE)										
5	HEX NUT		BRASS	GOLD	1	SHEET			1 OF 1				PART NO.								
4	LOCK WASHER		BRASS	GOLD	1								142191–75								
3	CONTACT PIN		BRASS	GOLD	1			CAD FILE		C:/142/142191–75.DWG		DWG. NO.		142191–75.DWG	REV.	A	SIZE	A	SCALE	NA	
2	INSULATOR		TEFLON	NATURAL	1																
1	BODY		BRASS	GOLD	1																
DESCRIPTION		MATERIAL		FINISH	QTY	DO NOT SCALE DRAWING															