

## Data Sheet | Item Number: 770-601

Fixing pin; 6 mm Ø, for 2.5 ... 4.0 mm mounting plates; Plastic; black

<https://www.wago.com/770-601>



Color: ■ black

### Mounting accessories WINSTA® MIDI

Realize the electrical installation easily and quickly: The mounting accessories from the WINSTA® MIDI product line is the solution for error-free electrical installation. You can rely on the quality of WINSTA® components from WAGO for your electrical installation accessories too. The WINSTA® MIDI Pluggable Connection System with Push-in CAGE CLAMP® spring pressure connection technology facilitates exemplary electrification. Due to the integrated test slot, connections can be checked even when they are plugged in. This saves time, labor, and money.

Lower costs through fast commissioning and elimination of service expenses – solutions from WINSTA® MIDI

WINSTA® is the pluggable connection system that is ideally tailored to the strict requirements of electrical installation. It allows error-free installation of cables and components, quickly and reliably. Now you can also lower installation expenses without compromising quality and safety: with protection against mismatching eliminates the need for servicing and prevents unnecessary downtime.

- pre-assembled versions
- convenient installation and commissioning

### Notes

General safety information

**NOTICE: Observe installation and safety instructions!**

1. Only to be used by a qualified electrician or by a person electrically instructed for the task (EIP per DIN VDE 0105-100).
  2. Do not install while energized or under load.
  3. Use only for its intended purpose.
  4. Observe applicable national regulations, standards and directives.
  5. Observe the technical specifications of the products.
  6. Ensure correct polarity assignment.
  7. Do not use damaged or contaminated components.
  8. Observe conductor types, conductor cross-sections, strip lengths and cable diameters.
  9. Insert conductors up to the stop.
  10. Use only with locking lever and strain relief.
  11. Use original accessories only.
- To be sold only with installation instructions!**

### Material data

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	black
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Weight	0.5 g

### Environmental requirements

Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

### Commercial data

Product Group	20 (Winsta)
PU (SPU)	250 pcs
Packaging type	Box
Country of origin	CN
GTIN	4045454636975
Customs tariff number	39269097900

### Product Classification

UNSPSC	31162301
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 9.0	EC002863
ETIM 10.0	EC002863
ECCN	NO US CLASSIFICATION

### Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

### Downloads

#### Environmental Product Compliance



##### Compliance Search

Environmental Product  
Compliance 770-601



### Documentation

#### Bid Text

770-601	19.02.2019	xml 2.60 KB	
770-601	09.01.2015	doc 22.50 KB	

CAD/CAE-Data

CAE data

WSCAD Universe  
770-601

