

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REV PER ECO 16-007588	6-13-16	CT	RL





SECTION A-A





RECOMMENDED PRINTED CIRCUIT BOARD LAYOUT
(CONNECTOR SIDE)

1. MARK AMP, PART NO., DATE CODE
2. NUMBERS INDICATING END POSITIONS MARKED THIS SIDE ONLY.
3. .000030 GOLD IN CONTACT AREA, SELECTIVE OVER NICKEL TIN ON CONTACT TAILS. CONTACT MATL: BRASS.
4. HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER MIL-M-24519, GLCP-30F; COLOR: GRAY.
5. FEATURE NOT PRESENT IN 20 THRU 50 POSITION.

2	Z	Y	X	U	NO OF CONTACTS	PART NO.
1-10	.450 [11.43]	9	1.150 [29.21]	.900 [22.86]	20	1-530733-1
1-15	.700 [17.78]	14	1.400 [35.56]	1.150 [29.21]	30	1-530733-0
1-64	3.150 [80.01]	63	3.850 [97.79]	3.600 [91.44]	128	530733-9
1-55	2.700 [68.58]	54	3.400 [86.36]	3.150 [80.01]	110	530733-8
1-50	2.450 [62.23]	49	3.150 [80.01]	2.900 [73.66]	100	530733-7
1-45	2.200 [55.88]	44	2.900 [73.66]	2.650 [67.31]	90	530733-6
1-40	1.950 [49.53]	39	2.650 [67.31]	2.400 [60.96]	80	530733-5
1-35	1.700 [43.18]	34	2.400 [60.96]	2.150 [54.61]	70	530733-4
1-30	1.450 [36.83]	29	2.150 [54.61]	1.900 [48.26]	60	530733-3
1-25	1.200 [30.48]	24	1.900 [48.26]	1.650 [41.91]	50	530733-2
1-20	.950 [24.13]	19	1.650 [41.91]	1.400 [35.56]	40	530733-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL 4 | FINISH 3

DWN T.WIEST 9-12-89
CHK D.GUTTER 11-20-91
APVD D.GUTTER 11-20-91
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT 0

TE Connectivity

NAME
ASSEMBLY,PIN HEADER, MINI-BOX
RIGHT ANGLE
—

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-530733	—

CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 1 | REV F

530733

1471-9 (1/15)

Downloaded from Arrow.com.