



TERMINALS & SPLICES

CRIMP RINGS & SPADES



✓ Active

TE CONNECTIVITY (TE)

SOLIS R 22-16 COMM 22-18 MIL 6

SOLISTRAND | SOLISTRAND

34110

TE Internal Number: 34110

Mil-Spec: M7928/7-3

EU RoHS Compliant

EU ELV Compliant

Terminal Type Ring Tongue

Stud Diameter 3.51 mm [.138 in]

Sealed No

Heavy Duty No

Wire Size (AWG) 22 – 16

PRODUCT DRAWING

English

3D PDF

DOCUMENTATION

Product Drawings

TERMINAL, RING TONGUE, SOLISTRAND

PDF

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Environmental Compliance

TE Material Declaration

MD_34110_04092014025_dmtec

PDF

English

Agency Approvals

UL Report

Plastic-Grip, Solistrand, DG, And PIDG Terminals

PDF

English

CSA Certificate

WIRE CONNECTORS, BUTT AND PARALLEL SPLICES, NON-INSULATED TYPE SOLISTRAND REPORT

PDF

English

UL

Plastic-Grip And Solistrand Terminal, Butt And Parallel Connectors

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Sealed No

Barrel Type Closed Barrel

Wire/Cable Type Regular Wire

Insulated No

Insulated Wire Support No

Stud Size 6, M3.5

Wire/Cable Composition Solid or Stranded

Shape Code RING-048

Configuration Features

Number of Holes 1

Body Features

Plating Material Copper, Tin

Inspection Slot No

Plating Thickness (µin) 100

Contact Features

Terminal Type Ring Tongue

Terminal Orientation Straight

Military Part Class Class II

Dimensions

Stud Diameter 3.51 mm [.138 in]

Wire Size (AWG) 22 – 16

Wire Size (mm²) .3 – 1.42

Wire Size (CMA) 509 – 3260

Barrel Inside Diameter 1.55 mm [.061 in]

Material Thickness .84 mm [.033 in]

Overall Length 15.77 mm [.621 in]

Barrel Inside Diameter (Min) 1.55 mm [.061 in]

Usage Conditions

Operating Temperature Range (°C) 170

Operation/Application

Heavy Duty No

Industry Standards

Government Qualified Yes

Packaging Features

Packaging Method Loose Piece

Packaging Quantity 1000

Statement of Compliance

Statement of Compliance

PDF
