



**Part Number :** [1300540021](#)

**Product Description :** Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, Unshielded PVC, 2.0m (6.56') Length

**Series Number :** 130054

**Status :** Obsolete

**Product Category :** Circular Industrial Connectors

**Engineering Part Number :** ERWPAB3002M020



---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

|                    |                    |
|--------------------|--------------------|
| GADSL/IMDS         | Product not active |
| China RoHS         | Product not active |
| EU ELV             | Product not active |
| Low-Halogen Status | Product not active |
| REACH SVHC         | Product not active |
| EU RoHS            | Product not active |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

|              |  |
|--------------|--|
| Status       | Obsolete   |
| Category     | Circular Industrial Connectors   |
| Series       | 130054   |
| Description  | Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, Unshielded PVC, 2.0m (6.56') Length |
| IP Rating    | IP67   |
| Product Name | RJ45, Ultra-Lock (M12)   |
| Type         | Double Ended   |
| UPC          | 78678804234  |

### Agency

|    |         |
|----|---------|
| UL | E200650 |
|----|---------|

### Electrical

|                               |            |
|-------------------------------|------------|
| Current - Maximum per Contact | 0.5A       |
| Voltage - Maximum             | 250V AC/DC |

### Physical

|                      |                     |
|----------------------|---------------------|
| Coupling Type        | Push to Lock        |
| Gender               | Female-Male         |
| Keyway               | D-Coded             |
| Length               | 2.0m                |
| Material - Component | Nickel-plated Brass |
| Mounting Thread Size | PG9                 |
| Net Weight           | 119.700/g           |
| Orientation          | Straight            |
| Panel Mount          | Back                |
| Poles                | 4                   |

|                               |                |
|-------------------------------|----------------|
| Temperature Range - Operating | -25° to +80°C  |
| Wire/Cable Type               | Unshielded PVC |
| Wire Size (AWG)               | 24             |

---

This document was generated on Jun 07, 2026

Obsolete