

 PRODUCTS ▾

 DISTRIBUTOR INVENTORY

 INDUSTRIES ▾

 SUPPORT ▾

 NEWS & EVENTS ▾

 ABOUT US ▾

3455RM 80020672

Products > Sensors > Humidity, Thermal & Flexible Heater Products > Thermostats/Thermal Switches > Commercial > Manual Reset > 3455RM Series > [3455RM 80020672](#)

Overview

3455RM Series Phenolic Manual Reset Thermostats.

The 3455RM Series consists of a temperature-sensitive bimetal disc, electrically isolated from the switch, which actuates the switch contacts.

[View More](#)



 view all 3455RM 80020672 literature

 view distributor inventory

 sample request

 email support

 get support

 email sales

 find a distributor

 email this page

Technical Specifications

Functional Properties	Open on rise	Reset Type	Manual
Operating Temperature	52 °C to 150 °C [125 °F to 302 °F]	Amperage	15 A/10 A resistive max.
Voltage	120 Vac/240 Vac	Open Temperature	98.9 °C [210 °F]
Open Tolerance	4.4 °C [8 °F]	Close Temperature	Manual
Close Tolerance	N/A	Environmental Exposure Range	10 °C to 150 °C [50 °F to 302 °F]

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 Commercial Thermostats	Datasheet	English	756KB
 Thermostats Line Guide	Product Line Guide	English	444KB
 Thermal Sensors	Product Range Guide	English	2MB

Product Features

- Cost effective
- Rivet sleeve construction
- Manually resettable
- High temperature capability

Applications

- HVAC
- Appliances
- Office automation

NAVIGATION LINKS

DISTRIBUTOR LINKS

LANGUAGE

ECOM LOGIN

PRODUCTS

DISTRIBUTOR INVENTORY

INDUSTRIES

SUPPORT

NEWS & EVENTS

ABOUT US

LEARN CENTER

REQUEST ACCESS TO ECOM

SALES/AD PORTAL LOGIN

SALES/AD PORTAL ACCESS REQUEST

SAMPLE REQUEST

SUPPLIER MICRO SITE

SOCIAL MEDIA



SITE INFORMATION

PRIVACY STATEMENT

SITEMAP

TERMS & CONDITIONS

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.