


ITEM NO.	DESCRIPTION	QTY.
1	WIRE	1
2	MPM-V00-0A2-2P13-E00	1
3	OVERMOLDING	1
4	USB A-2.0	1

REVISIONS			
REV.	DESCRIPTION	DATE	BY
1	ORIGINAL	DRAWN DATE	







SPECIFICATIONS

CURRENT RATING:	1.5A
VOLTAGE RATING:	12V
WITHSTANDING VOLTAGE:	500V
INSULATION RESISTANCE:	1000MΩ MIN FOR 1 MIN
CONTACT RESISTANCE:	50mΩ MAX
TEMPERATURE RANGE:	-25°C TO 60°C
INSULATOR MATERIAL:	HTN
INSULATOR COLOR:	BLACK
CONTACT MATERIAL	BRASS
CONTACT PLATING	5μ" GOLD PLATING
MAGNET MATERIAL:	N35
MATING CYCLES:	10000
STROKE:	1.1 MM
CONTACT FORCE:	80±20 g
MATING PARTS:	MPF-V00-0A2-2R13-E00

CABLE SPECIFICATIONS

CABLE MATERIAL:	PVC
CABLE COLOR:	BLACK
OVERMOLDING MATERIAL:	PVC
OVERMOLDING COLOR:	BLACK
OPPOSITE END	USB A-2.0

POGO PIN	WIRE COLOR	USB PIN NO.	SIGNAL
1	RED	1	VCC
-	-	2	-
-	-	3	-
2	BLACK	4	GND

NOTE:IR REFLOW AND WAVE SOLDERING NOT RECOMMENDED AS THE PROCESSES CAN DEMAGNETIZE THE CONNECTOR MAGNETS.

RoHS COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC, AND SHALL NOT BE REPRODUCED , OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN BY	V.K.
DRAWN DATE	08/21/2025
CHECKED BY	R.S.M.
CHECK DATE	08/21/2025

TOLERANCES	
.X	±0.5
.XX	±0.2
.XXX	±0.1

ALL DIMENSIONS AND TOLERANCES IN MM

MALE CABLE ASSEMBLY, CIRCULAR, 14.6 MM DIA, 2 POSITIONS

PART NUMBER	MCM-Y00-2G2-2P13-BV0		
MATERIAL		SIZE	A
		REVISION	1
SCALE	1:1.5	SHEET	1 OF 1

Downloaded from Arrow.com.