Part Number : 191640018
Product Description : Perma-Seal Female Quick Disconnect Receptacle for 22-18 AWG Wire, Tab Size 6.35 x 0.81mm, Mylar Tape Carrier
Series Number : 19164
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : SAA-9261T



Documents and Resources

Drawings

191640018_sd.pdf

Specifications

PS-19902-011-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19164
Description	Perma-Seal Female Quick Disconnect Receptacle for 22-18 AWG Wire, Tab Size 6.35 x 0.81mm, Mylar Tape Carrier
Product Name	Perma-Seal
Type	Standard Quick Disconnect
UPC	800753113060

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed
Color - Resin	Red
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	NiAc
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin

Downloaded from Arrow.com.

Material - Resin	Nylon
Net Weight	1.733/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	4.32mm max.
Wire Size (AWG)	18, 20, 22

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880095

Downloaded from Arrow.com.