

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=10136645-0321LF* > 10136645-0321LF

10136645-0321LF

10136645-0321LF - Minitek® Pwr4.2 : Minitek® Pwr4.2 Plug Housing, Single row, 3 positions, Non Glow Wire Compatible, Natural Color



Customer drawing

Product Environmental Compliance Report

ACTIVE

RoHS Compliant

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Specifications

Download document

General Dimensional Electrical Mechanical Physical Approvals / Certifications Other Features	
General	
Number of contacts	3
Series	10136645
Dimensional	
Pitch	4.2
Electrical	
Withstanding Voltage	1500 Vac, No breakdown. Current leakage < 5mA
Current rating	UP to 9 Amps
Resistance (Contact)	10 milliohm max.
Resistance (Insulation)	1000M ΩMin
Voltage rating	600V
Mechanical	
Durability (Mating cycles)	30 Cycles
Insertion force	14.7N max.
Withdrawal Force	1 N min.
Glow Wire Compatible	No
Physical	
Color (Housing)	Natural
Material (Contact)	Brass
Material (Housing)	Nylon 66
Temperature (Range)	-40°C to +105°C
Approvals / Certifications	
Approvals / Certifications	Pending
Other Features	
Packaging (Type)	Tray

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.