



Representative Image

Catalog No. H125-TB

Description: 1-1/4 INCH ZINC CONDUIT HUB

UPC No 786210899534

Home > Cable Protection Systems > T&B Rigid Fittings > Electrical fittings

1-1/4 Inch Zinc Hub Connector with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

Descriptors

Category	Electrical fittings
Special Features	Sealing Ring and Groove with Innovative Profile Better Than Standard O-Ring
Application	To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure

Specifications

Material	Zinc
Temperature Rating	105 C

Classifications

Brand Name	T&B Rigid Fittings
Standard	UL E23018, CSA UL E23018, CSA

Dimensions

Size	1-1/4 Inch
------	------------

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Zinc die-cast

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y