


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00024	Connector, dc plug, 5.5x2.1xL23 mm, molding style, spring contacts	1	
2	Adapter	Car adapter	1	7.5 A fuse
3	30-00686	Wire, 2C TS, 20 AWG, UL2464, 300V, 80C, 4.70 mm, VW-1, PVC	1	
4	24-00182	Overmold, dc plug, 5.5 mm, Tensility	1	PVC, black



Notes:
Functionally equivalent components may be substituted

Wiring Diagram		
50-00024	wire color	Car adapter
center	red	+
sleeve	black	-

Revision:	Date:	Description:	Prepared:	Notes:	TENSILITY tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com
A	9/23/2019	Initial release	Verified:		
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description:	Size: Part number:
				Cable, 1830 mm, 5.5x2.1x12 mm 50-00024 dc plug to car adapter, 20 AWG, UL2464, 30-00686 wire	A 10-03576
					Scale: 2:3  Sheet 1 of 1