

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=10133304-001LF* > 10133304-001LF

10133304-001LF

10133304-001LF - USB : USB type A to Micro USB type B cable , Black color, 200mm length, Gold Flash plating



ACTIVE

RoHS Compliant

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Customer drawing

Product Environmental Compliance Report

Specifications

Download document

Dimensional General Electrical Mechanical Physical	
Dimensional	
Length (Overall)	200 mm
General	
Product Type	Cable Assembly
Series	10133304
Electrical	
Current rating	1A per contact for Micro USB 1.5A per contact for standard USB
Resistance (Insulation)	1000 MΩ min
Resistance (LLCR - Low Level Contact Resistance)	30 mΩ max
Voltage rating	30VAC
Mechanical	
Durability (Mating cycles)	1500 cycles for standard USB 10000 cycles for Micro USB
Contact unmating force	10N min. for standard USB 8N min. for Micro USB
Mating force	35N max
Physical	
Temperature (Operating - range)	-30°C~+80°C

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.