


	5	4	3	2	1
D		Description:	CAT5E molded & booted patch cable		DRAWING NO. 73-779X-XXX-CUST
		Part No:	73-779X-XXX		REVISIONS
		Application:	Patch cable		01 OFFICIAL RELEASE
C		Crimp Tool:	N/A		03-28-11 J J J D
		Impedance:	N/A		
		Frequency Range:	N/A		
B		Material:	Plug	RJ-45, Gold plated on contacts	
			Hood	PVC	
			Cable	UTP, 24 AWG, 4 twisted pairs, stranded bare copper, UL ETL EIA/TIA-568B verified category 5e	
A		RoHS Compliance:	Yes		
		Technical Detail:	N/A		
		TABLE 1			
		PIN ASSIGNMENT			
		RJ-45 PLUG RJ-45 PLUG			
		1 2 3 4 5 6 7 8			
		X=COLOR			
		0-GRAY			
		1-BLACK			
		2-BLUE			
		3-GREEN			
		4-RED			
		5-YELLOW			
		6-WHITE			
		7-ORANGE			
		8-PINK			
		9-PURPLE			
		PART NUMBER		LENGTH (FEET)	DESCRIPTION
		73-779X-1		1	CAT5E MOLDED & BOOTED PATCH CABLE, 1FT
		73-779X-1.5		1.5	CAT5E MOLDED & BOOTED PATCH CABLE, 1.5FT
		73-779X-3		3	CAT5E MOLDED & BOOTED PATCH CABLE, 3FT
		73-779X-5		5	CAT5E MOLDED & BOOTED PATCH CABLE, 5FT
		73-779X-7		7	CAT5E MOLDED & BOOTED PATCH CABLE, 7FT
		73-779X-10		10	CAT5E MOLDED & BOOTED PATCH CABLE, 10FT
		73-779X-14		14	CAT5E MOLDED & BOOTED PATCH CABLE, 14FT
		73-779X-25		25	CAT5E MOLDED & BOOTED PATCH CABLE, 25FT
		73-779X-50		50	CAT5E MOLDED & BOOTED PATCH CABLE, 50FT
		73-779X-100		100	CAT5E MOLDED & BOOTED PATCH CABLE, 100FT
		Pin 1			
		Cable Length			
		DIM OUTLINE			
		受控 CONTROLLED DOCUMENT			
		编号 P/N 73-779X-XXX-CUST		版本 Rev 01	日期 Rel'd Date Jul11,11
		TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY JEAN.JIN	DATE 03-28-11
		DECIMALS mm		CHECKED BY JEAN.JIN	DATE 03-28-11
		X ± 0.5		APPROVED BY DONALD	DATE 03-28-11
		X.X ± 0.3			
		X.XX ± 0.15			
		ANGLES ± 0.5°		U/M mm	
		THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.			
		CUSTOMER COPY			
		cinch CONNECTIVITY SOLUTIONS a bel group			
		TITLE CAT5E MOLDED & BOOTED PATCH CABLE			
		SHEET 1 OF 1		DRAWING NO. 73-779X-XXX-CUST	SIZE A