



OGA DIAG: 56.27 [1429.3]
AA DIAG: 55.16 [1401.2]

KIT 98 SKU NUMBER	TYPE	PRODUCT SPEC
98-0003-3625-9	DX123	33626/34017



SECTION A-A
SCALE: 8/1

J1 PINOUT	
1	CH 3
2	CH 2
3	PWR
4	2.5V
5	GRD
6	PWR
7	CH 0
8	CH 1

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 4643 ±10%
2. 8 PIN AMP CONNECTOR
LATCH STYLE HOUSING P/N: 487526-7
TIN CONTACTS P/N: 2-487406-4
HOUSING ORIENTED WITH LATCH UP
3. GASKET ON SENSOR BACKSIDE

INCHES [MM]
1/8" [3.18]
1/4" [6.35]
3/8" [9.53]
1/2" [12.70]
5/8" [15.88]
3/4" [19.05]
7/8" [22.23]
1" [25.40]

3M	3M TOUCH SYSTEMS WATUQUIL, MA USA
THIS DOCUMENT IS THE PROPERTY OF 3M. IT IS TO BE USED ONLY FOR THE PURPOSES FOR WHICH IT WAS ORIGINALLY DESIGNED. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT PERMISSION IN WRITING FROM 3M.	
DATE	MTD 8/19/10
DO NOT SCALE DRAWING	
SCALE	1 = 1

B	REVISE PER CO 032628	3/11	MTD
01	RELEASE PER CO 031908	8/10	MTD
MKT DWG DST2270DX 55.16"			
AUTOCAD			
1 OF 1			
38043-MKT			
B			