

Technical data sheet

Article number:
126-00196

LRT18RWPM4.8

Product Group	1-piece fixing ties with arrowhead, with wings
Product Family	for round holes, releasable
Material	Polyamide 6.6 V0 (PA66V0)
Colour	White (WH)
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7SP, EVO7i, EVO7iSP
Bundle Ø max.	20 mm
Bundle Ø min.	1 mm
Fixation Method	arrowhead
Flammability	UL 94 V0
for Hole Ø (FH)	4.7 - 4.9 mm
Length (L)	110 mm
Min.Tensile Strength	100 N
Operating Temperature	-40 °C to +105 °C
Package Content	100 pcs.
Package Content packed in	bag
Panel Thickness max.	2.0 mm
Panel Thickness min.	0.4 mm
ROHS compliant	Yes
Specifications	ANSI/UL 1565, ANSI/UL 62275
Thickness (T)	1.1
UL-File Number	E64962
Width (W)	2.5 mm

