Part Number : 731570040
Product Description : Precision Test Adapter, 1.85mm Plug-to-1.85mm Jack, Straight, Passivated, 67 GHz, 50 Ohms
Series Number : 73157
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

731570040_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

Downloaded from Arrow.com.

General

Status	Active
Category	RF / Coaxial Connectors
Series	73157
Description	Precision Test Adapter, 1.85mm Plug-to-1.85mm Jack, Straight, Passivated, 67 GHz, 50 Ohms
Application	RF
Product Name	Precision Test - 1.85mm
Style	Adapter, Within-Series Adapter
Type	Subminiature
UPC	196823316463

Electrical

Frequency	67 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 150 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack/Plug
Keying to Mating Part	N/A
Net Weight	4.188/g
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
PCB Thickness - Recommended	N/A
Reverse Polar	No
Wire/Cable Type	N/A

Downloaded from Arrow.com.