





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/23/08	
A		REVISED SPEC.	7/3/12	

NUMBER OF POSITIONS	DIM. A	DIM. B
02	.118 [3.00]	.275 [7.00]
03	.236 [6.00]	.394 [10.00]
04	.354 [9.00]	.512 [13.00]
05	.472 [12.00]	.629 [16.00]
06	.591 [15.00]	.748 [19.00]
07	.709 [18.00]	.866 [22.00]
08	.827 [21.00]	.984 [25.00]
09	.954 [24.00]	1.102 [28.00]
10	1.063 [27.00]	1.220 [31.00]
11	1.181 [30.00]	1.340 [34.00]
12	1.299 [33.00]	1.456 [37.00]



SPECIFICATIONS:

Material:

Insulator: Nylon, rated UL 94V-0

Insulator color: Black

Electrical:

Operating voltage: 250 VAC RMS max

Current rating: 20 Awg: 5 Amps max

22 Awg: 5 Amps max

24 Awg: 4 Amps max

26 Awg: 3 Amps max

28 Awg: 2 Amps max

30 Awg: 1 Amp max.

Insulation resistance: 1000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1500 VAC for 1 minute

Mechanical:

Wire size: 20 Awg thru 30 Awg

Temperature Rating:

Operating temperature: -40°C to +120°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE: FEMALE CRIMP HOUSING, SINGLE ROW

.118 [3.00] PITCH

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED			
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010
APPROVALS		DATE	
DRAWN	DY	9/23/08	
CHECKED			
APPROVED			
SIZE	PART NO.	REV.	
X	DMT-1-XX	A	
REF:	S00123T	SCALE:	NTS
		SHEET	1 OF 1

A

B

C

D