






HARTING P/N	LENGTH (L)
33152430100102	100 ± 3
33152430200102	200 ± 5
33152430300102	300 ± 5
33152430400102	400 ± 5
33152430500102	500 ± 10
33152432000102	2000 ± 50

WIRING TABLE

C1	WIRE	C2
1	AWG30	1
2	AWG30	2
3	AWG30	3
-	AWG30	-
11	AWG30	11
12	AWG30	12

- NOTES:
- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT TEST.
 - 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
 - 3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG,THEN PUT IT INTO THE CARTON(QTY ACCORDING TO ACTUAL CONDITION)
 - 4.)WHITE LABEL CONTENT:

DATE CODE
HARTING P/N

	All rights reserved Department HCS - CN HARTING Customised Solutions D-32339 Espelkamp	All Dimensions in mm Original Size DIN A3	Scale 2:1	Free size tol.	Ref.	
					Sub.	
	All rights reserved Department HCS - CN HARTING Customised Solutions D-32339 Espelkamp	Created by LINI Lin	Inspected by QINL Qin	Standardisation QINL Qin	Date 2020-12-08	State Final Release
		Title Har-flex 12Pole,dul-end,with SR,L=XX MM		Rev. C		Page 1/1
		Type TB		Number 33150012		