

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 (A)
- M12 (B)
- M12 (D)
- M12 (I)
- M12 (K)
- M12 (L)
- M12 (S)
- M12 (T)
- M12 (X)
- M23
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >




M12A-12BFFM-SR8B01

Operating Temperature: -20°C ~ +80°C
Transmission Speed: N/A
Shielded: Metal, Non-shielded
Jacket Material: PUR
Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart


 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories


Connector Type ▼ Search



M Series....
CAP-WBDF SMA1
-40°C ~ +105°C

- 0 +


☐



M Series....
CAP-WBDF SMA2
-40°C ~ +105°C

- 0 +


☐



M Series....
CAP-WBDF SPB1
-40°C ~ +105°C

- 0 +


☐



M Series....
IA-A12M-A12M
-20°C ~ +85°C

- 0 +


☐



M Series, M12, A...
M12A-12PMMP
-40°C ~ +105°C

- 0 +

☐




M Series, M12, A...
M12A-12PMMS
-20°C ~ +85°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 1.5A	Connector Type Overmolded
Shielded Metal, Non-shielded	No. of Contacts 12
Connector Gender Female	Backshell Straight
Mating Style Screw Thread	IP Rating IP68
Assembly Style N/A	
<div> More Options</div>	

People Also Bought



M12A-12BFFM-SR8B01



MSBP05ML-SBPFL-01



AB-BB03BL-BBBL-01



AB-CB008FL-CB0FL-01



BP-04AMMM-SR7B01