

Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 3 ft. (0.91 m), White

MODEL NUMBER: P018-003-AWH



Connects a PDU or UPS system with a C14 input port to network hardware, such as computers, servers and storage drives, with C15 power connectors.

Features

Safe, Reliable Power Solution

- Connects PDU or UPS system with C14 input to network hardware with C15 power connectors
- Ideal for replacing an old or lost cord
- Recommended for Cisco, HP and other C15-compatible hardware

Color-Coded Cable and Connectors

- Colored white for easy identification in crowded rack or workstation

Optimum Construction

- 14 AWG wire
- Flexible SJT jacket
- 250V/15A rating
- UL-listed

Specifications

OVERVIEW	
UPC Code	037332199140
Device Compatibility	Network Switch; UPS; PDU
Country/Region	North America
INPUT	

Highlights

- Easy-to-identify white SJT jacket and fully molded white ends
- Flexible 14 AWG wire for easy routing
- 250V/15A rating
- UL-listed
- Recommended for Cisco®, HP and other C15-compatible hardware

Package Includes

- P018-003-AWH Heavy-Duty Computer Power Cord, White, 3 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C15
PHYSICAL	
Plug Color	White
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.2mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (cm)	91.44
Shipping Dimensions (hwd / in.)	9.90 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	25.15 x 17.78 x 1.27
Shipping Weight (lbs.)	0.44
Shipping Weight (kg)	0.20
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.