

Han CGM-P M25x1,5 D.13-18mm black



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5193
Specification	Han CGM-P M25x1,5 D.13-18mm black
HARTING eCatalogue	https://b2b.harting.com/19000005193

Identification

Category	Accessories
Series of hoods/housings	Han® CGM-P
Type of accessory	Cable gland

Technical characteristics

Tightening torque	≤5 Nm (depending on the cable and the seal insert used)
Wrench size	33
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M25
Clamping range	13 ... 18 mm
Width across corners	36.5 mm

Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 514B QCRV.E479780 CSA-C22.2 No. 18.3 QCRV7.E479780

Commercial data

Packaging size	10
Net weight	23 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27144432 Screwed cable gland (electr.)