

[Harnessing](#) > [Heat Shrink Components](#) > [EMI Shielded Boots](#)

202S163-25C-0

✓ ACTIVE

[Raychem](#) | [Raychem Rayaten](#)

TE Part # **202S163-25C-0**

TE Internal #: **EK7286-000**

Molded Part Type : **EMI Shielded Molded Parts**

Color : **Black**

Material Systems Code : **25**

Material : **Modified Elastomer**

Adhesive Pre-Coat : **No**

 Add to List ▾

[Similar Products](#)

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America ▾

Request pricing, availability and customization options

CONTACT US



We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

202S163-25C-0

 [202S163-25C-0](#) English

Catalog Pages/Data Sheets

 [ENG_DS_1-1773953-5_0518.pdf](#) English

Product Environmental Compliance

Safety Data Sheet

 [ENG_MSDS_SDS0281-CA-ENG_1.0.pdf](#) English

 [FRE_MSDS_SDS0281-CA-FRE_1.0.pdf](#) French

Safety Data Sheet

 [GER_MSDS_SDS0281-EC-GER_1.0.pdf](#) German

Safety Data Sheet

 [DAN_MSDS_SDS0281-EC-DAN_1.0.pdf](#) Danish

Safety Data Sheet

 [ENG_MSDS_SDS0281-EC-ENG_1.0.pdf](#) English

Safety Data Sheet

 [SPA_MSDS_SDS0281-EC-SPA_1.0.pdf](#) Spanish

Safety Data Sheet

 [FRE_MSDS_SDS0281-EC-FRE_1.0.pdf](#) French

Safety Data Sheet

 [ITA_MSDS_SDS0281-EC-ITA_1.0.pdf](#) Italian

Safety Data Sheet

 [DUT_MSDS_SDS0281-EC-DUT_1.0.pdf](#) Dutch

Safety Data Sheet

 [NOR_MSDS_SDS0281-EC-NOR_1.0.pdf](#)

Safety Data Sheet

[SWE_MSDS_SDS0281-EC-SWE_1.0.pdf](#) Swedish

Safety Data Sheet

[ENG_MSDS_SDS0281-US-ENG_1.0.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type : **EMI Shielded Molded Parts**

Angle : **Straight**

Product Type : **Molded Part**

Body Features

Color : **Black**

Material Systems Code : **25**

Material : **Modified Elastomer**

Adhesive Pre-Coat : **No**

Material Code : **25**

Dimensions

Expanded Inside Diameter (Min) : **43 mm [1.69 in]**

Recovered Inside Diameter (Max) : **28.2 mm [1.11 in]**

Cable Diameter Range : **10.5 – 22.1 mm [.41 – .87 in]**

Usage Conditions

Operating Temperature Range (°C): **-75 – 150**

Other

Adhesive Type : **Adhesive Purchased Separately**

Statement of Compliance

[Statement of Compliance pdf](#)

Compatible Parts [> Contact Product Support](#)

Also in the Series | [Raychem Rayaten](#)



EMI Shielded Boots
(91)