**Part Number :** 2005280061
**Product Description :** Easy-On FFC/FPC Connector, 1.00mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 6 Circuits, 150°C Operating Temperature, Gold over Nickel Plating
**Series Number :** 200528
**Status :** Active
**Product Category :** FFC / FPC Connectors



## Documents and Resources

### Drawings

2005280061_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

2005289200-200.pdf

2005280001-PS-000.pdf

2005280300-TS-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44; 34; 33 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | FFC / FPC Connectors |
| Series | FD19 |
| Description | Easy-On FFC/FPC Connector, 1.00mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 6 Circuits, 150°C Operating Temperature, Gold over Nickel Plating |
| Comments | Black Actuator |
| Product Name | Easy-On |
| UPC | 191128822251 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum | 125V |

### Physical

| | |
|---|---|
| Actuator Type | Front Flip |
| Circuits (Loaded) | 6 |
| Color - Resin | Beige |

Downloaded from Arrow.com.

| | |
|---|---|
| Contact Position | Bottom |
| Durability (mating cycles max) | 20 |
| Mated Height | 1.90mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Gold |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Net Weight | 106.100/mg |
| Orientation | Right Angle |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Mounting | Surface Mount |
| PCB Retention | No |
| Pitch - Mating Interface | 1.00mm |
| Pitch - Termination Interface | 1.00mm |
| Plating min - Mating | 0.051µm |
| Plating min - Termination | 0.051µm |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +150°C |
| Wire/Cable Type | FFC/FPC |



Downloaded from Arrow.com.