

Search within category

GO

BUY NOW

DESIGN / INSTALL



ISTPH6X3.5MTL

Patch Cord, IndustrialNET, Cat6A, Shielded, 600V, RJ45 plug to RJ45 plug, Teal, 3.5 meter

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Conductor Gauge (AWG)	NA			
Conductor Gauge (kcmil)	26			
Performance Level	Category 6A			
Conductor Type	Stranded			
Cable Construction	NA			
Patch Cord Type	Shielded			
Plug Housing Material	Polycarbonate			
Jacket Material	Thermoplastic Elastomer			
Connector 2 Type	Modular Plug			
Connector 1 Type	Modular Plug			
Overall Length (In.)	138.6			
Overall Length (ft.)	11.55			
Overall Length (m)	3.5			
Overall Length (mm)	NA			
Nominal Diameter (In.)	0.29			
Nominal Diameter (mm)	7.4			
Wiring Scheme	T568B			
Maximum Operating Temperature (°C)	60			
Maximum Operating Temperature (°F)	140			
Minimum Operating Temperature (°C)	-10			
Minimum Operating Temperature (°F)	14			
Maximum Storage Temperature (°C)	70			
Maximum Storage Temperature (°F)	158			
Minimum Storage Temperature (°C)	-40			
Minimum Storage Temperature (°F)	-40			
Boot Color	NA			
Color	Teal			
Sub Brand	IndustrialNet			

Flammability Rating	CM
Standards Met	ANSI/TIA-568-C.2 Category 6A and ISO 11801 Class Ea standards at swept frequencies up to 500MHz;ANSI/TIA-968-A requirements; IEC 60603-7 UL-rated: UL 1863; IEEE 802.3af and IEEE 802.3at for PoE applications
IP Rating	IP 20
NEMA Rating	NA
IEC Variant	IEC 60603-7
PoE Compatibility	PoE+
Product Type	Industrial Copper Patch Cord
RoHS Compliancy Status	Compliant
Min. Order Qty.	1
Measurement System	Meters (Rest of World)

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)