




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECR-22-133159	12MAY2022	P.C	D.Z


POSITION 1
IDENTIFICATION
FEATURE




MATERIAL: HOUSING: NYLON, UL94V-0
CONTACTS: BRASS, TIN-PLATED



24	46.2±0.25 [1.82±.01]	51.6 [2.03]	55.6 [2.19]	2-2029173-4
22	42.0±0.25 [1.65±.01]	47.4 [1.87]	51.4 [2.02]	2-2029173-2
20	37.8±0.25 [1.49±.01]	43.2 [1.70]	47.2 [1.86]	2-2029173-0
18	33.6±0.25 [1.32±.01]	39.0 [1.54]	43.0 [1.69]	1-2029173-8
16	29.4±0.25 [1.16±.01]	34.8 [1.37]	38.8 [1.53]	1-2029173-6
14	25.2±0.25 [.99±.01]	30.6 [1.21]	34.6 [1.36]	1-2029173-4
12	21.0±0.25 [.83±.01]	26.4 [1.04]	30.4 [1.20]	1-2029173-2
10	16.8±0.13 [.66±.005]	22.2 [.87]	26.2 [1.03]	1-2029173-0
8	12.6±0.13 [.50±.005]	18.0 [.71]	22.0 [.87]	2029173-8
6	8.4±0.13 [.33±.005]	13.8 [.54]	17.8 [.70]	2029173-6
4	4.2±0.13 [.17±.005]	9.6 [.38]	13.6 [.54]	2029173-4
2	-	5.4 [.21]	9.4 [.37]	2029173-2
POS	A	B±0.25 [.01]	C±0.38 [.015]	PART NUMBER



PCB LAYOUT: COMPONENT SIDE
RECOMMENDED BOARD THICKNESS 1.78 [.070]



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN K. WHITAKER 28AUG2008		 TE Connectivity			
DIMENSIONS: mm [INCHES]			CHK C. CASH 28AUG2008					
			APVD C. CASH 28AUG2008		NAME VERTICAL HEADER, WITH PEGS, WITHOUT DRAIN HOLES, 94V-0, VAL-U-LOK(TM)			
			TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.13 [.005] 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ±					
			PRODUCT SPEC					
			APPLICATION SPEC					
MATERIAL 			FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			WEIGHT 0.000000		A2	00779	C-2029173	—
CUSTOMER DRAWING					SCALE	10:1	SHEET 1 of 1	REV B