Data Sheet | Item Number: 2092-1602/002-000


Gripping plate with sliding connector release; for female and male connectors; 2 parts; Pin spacing 5 mm; light gray

https://www.wago.com/2092-1602/002-000



Color: light gray

Similar to illustration



Pole No.	A	B	C	D	E
2	7	1,5	–	20	–
3	12	1,5	–	20	–
4	12	1,5	–	20	–
5	22	1,5	3,5	25	9
6	22	1,5	3,5	25	9
7	22	6,5	3,5	25	9
8	22	6,5	3,5	25	9
9	42	1,5	5,0	35	19
10	42	1,5	5,0	35	19
12	42	6,5	5,0	35	19

Dimensions in mm

Physical data

Pin spacing	5 mm / 0.197 inches
Width	22 mm

Mechanical data

Design	with sliding connector release

Material data

Note (material data)	Information on material specifications can be found here
Color	light gray
Fire load	0.017 MJ
Weight	0.6 g

Commercial data

PU (SPU)	100 (25) pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821447009
Customs tariff number	85389099990

Downloaded from Arrow.com.

Product Classification

UNSPSC	39121421
eCl@ss 10.0	27-14-11-92
eCl@ss 9.0	27-14-11-92
ETIM 9.0	EC002848
ETIM 10.0	EC002848
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 2092-1602/002-000


Documentation

Additional Information

Technical Section	03.04.2019	pdf 2027.26 KB	

Installation Notes

Strain relief



Gripping plates are suitable for factory and field assembly.

Downloaded from Arrow.com.