



# lumbergautomation

A **BELDEN** BRAND



## DeviceNet Power Supply Cables

0905 203 302 | 0905 203 301



[0905 203 302/0.6 M](#)

Double-ended with 7/8" male connector and 7/8" female connector, 3 poles, 0.6 M.

[0905 203 301/... M](#)

Single-ended with 7/8" female connector, 3 poles.

### Electrical

Current rating 8 A  
Voltage rating 300 V

0905 356 312 | 0905 356 311 | 0905 356 313



[0905 356 312/0.6 M](#)

Double-ended with 7/8" male connector and 7/8" female connector, 4 poles, 0.6 M.

[0905 356 311/... M](#)

Single-ended with 7/8" female connector, 4 poles.

[0905 356 313/... M](#)

Single-ended with 7/8" male connector, 4 poles.

### Electrical

Current rating 8 A  
Voltage rating 300 V

0905 356 305 | 0905 356 304 | 0905 356 306



[0905 356 305/0.6 M](#)

Double-ended with 7/8" male connector and 7/8" female, 90° connector, 4 poles, 0.6 M.

[0905 356 304/... M](#)

Single-ended with 7/8" female, 90° connector, 4 poles.

[0905 356 306/... M](#)

Single-ended with 7/8" male, 90° connector, 4 poles.

### Electrical

Current rating 8 A  
Voltage rating 300 V

| 7/8" Male/Female 3-Poles | Leads        |
|--------------------------|--------------|
| Pin 1                    | green/yellow |
| Pin 2                    | 1            |
| Pin 3                    | 2            |

| 7/8" Male/Female 4-Poles | Leads        |
|--------------------------|--------------|
| Pin 1                    | 1            |
| Pin 2                    | 2            |
| Pin 3                    | green/yellow |
| Pin 4                    | 3            |

| 7/8" Male/Female 4-Poles (90°) | Leads        |
|--------------------------------|--------------|
| Pin 1                          | 1            |
| Pin 2                          | 2            |
| Pin 3                          | green/yellow |
| Pin 4                          | 3            |

| Part Number        |                    | Standard Cable Lengths |  |
|--------------------|--------------------|------------------------|--|
| 0905 203 302/0.6 M |                    |                        |  |
| 0905 203 301/...M  |                    | 5 M   10 M   15 M      |  |
| 0905 356 312/0.6 M | 0905 356 305/0.6 M |                        |  |
| 0905 356 311/... M | 0905 356 304/... M | 5 M   10 M   15 M      |  |
| 0905 356 313/... M | 0905 356 306/... M | 5 M   10 M   15 M      |  |