



Part Number : [734154491](#)

Product Description : MCX Plug, Straight, Crimp, RG-179 Cable, Die Cast Body, Gold (Au) Plated, One Piece Per Bag, 75 Ohms

Series Number : 73366

Status : Active

Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

[734154491_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[735970700-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Plug, Straight, Crimp, RG-179 Cable, Die Cast Body, Gold (Au) Plated, One Piece Per Bag, 75 Ohms
Application	RF
Product Name	MCX
Style	Cable
Type	Microminiature
UPC	884982691544

Electrical

Frequency	6 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	2.400/g
Orientation	Straight

Packaging Type	Individual Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-179

This document was generated on Dec 26, 2025