

**Part Number :** [936011686](#)

**Product Description :** Heavy-Duty Harsh Environment (HE) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 10B «57x27», M32 Thread , High Construction, Black

**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Connectors

**Engineering Part Number :** 7810.6485.6



---

## Documents and Resources

### Drawings

[936011686\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant                                  |
| China RoHS         | Not Reviewed per SJ/T 11365-2006              |
| EU ELV             | Not Relevant                                  |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21               |
| REACH SVHC         | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS            | Not Reviewed per EU 2015/863                  |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

|                |  |
|----------------|--|
| Status         | Active   |
| Category       | Heavy Duty Connectors  |
| Series         | 93601  |
| Description    | Heavy-Duty Harsh Environment (HE) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 10B «57x27», M32 Thread , High Construction, Black |
| Component Type | Double Lever Hood  |
| IP Rating      | IP66   |
| Product Name   | Heavy-Duty Connectors  |
| Standard       | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984  |
| Type           | HE   |
| UPC            | 887191842110   |

#### Agency

|     |         |
|-----|---------|
| CSA | 256883  |
| UL  | E249674 |

#### Electrical

|                   |      |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

#### Physical

|                     |                  |
|---------------------|------------------|
| Component Size      | 10B «57X27»      |
| Entry Location      | Side             |
| Hood Coating        | Polyester Powder |
| Hood Color          | Black RAL 9005   |
| Lock to Mating Part | Yes              |

|                 |                   |
|-----------------|-------------------|
| Material - Hood | Die-cast Aluminum |
| Material - Peg  | Stainless Steel   |
| Net Weight      | 189.330/g         |
| Number of Pegs  | 4                 |
| Packaging Type  | Bag               |
| Thread Size     | M32               |
| Thread Type     | (M) Metric        |

## Mates With / Use With

### Use with Part(s)

| Description | Part Number   |
|-------------|---|
| Use With    | Size 10B «57x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts |

---

This document was generated on May 20, 2026